


HC-B 10-TFL-52/O1M20S

Order No.: 1604760



HEAVYCON sleeve housing B10, for single locking latch, height 45 mm, with support 1x M20, lateral conductor exit

Commercial data

| | |
|--------------------------|---|
| GTIN (EAN) |  4 017918 881054 |
| sales group | D002 |
| Pack | 10 pcs. |
| Customs tariff | 85389099 |
| Catalog page information | Page 570 (PC-2011) |

Product notes

WEEE/RoHS-compliant since:
01/31/2006



<http://www.download.phoenixcontact.com>
Please note that the data given here has been taken from the online catalog. For comprehensive information and data, please refer to the user documentation. The General Terms and Conditions of Use apply to Internet downloads.

Technical data**General data**

| | |
|--------|--|
| Note | For contact inserts HC-B10, BB18, DD42, M, K8/24 |
| Design | B10 |
| Height | 52 mm |
| Width | 43 mm |
| Length | 73 mm |

| | |
|----------------------------------|--------------------------|
| Housing type | Sleeve housings |
| Locking type | for single locking latch |
| No. of cable exits | 1 |
| Cable exit | Lateral |
| Pg screw connection | None |
| Type of the screw connection | 1x M20 |
| Degree of protection for housing | IP65 |
| Ambient temperature (operation) | -40 °C ... 125 °C |
| Housing material | Aluminum, die-cast |
| Housing surface material | Powder-coated, gray |

Certificates / Approvals



Certification

GOST

Diagrams/Drawings

Dimensioned drawing

