



## Datasheet

ENGLISH

Stock No: 163-5348

# RS Pro Tachometer, Best Accuracy $\pm 0.05\%$ Contact, Optical LCD 100000 rpm, 19999 rpm



Measurement range	5 to 99999rpm (optical) 0.5 to 19999rpm (contact)
Resolution	0.1rpm
Accuracy	$\pm 0.05\%$ +1 digit (dependent on ambient light conditions)
Sensing range	50 to 150mm
Overall dimensions	215 x 65 x 38mm (H x W x D)
Battery	4 x AA Cells (not supplied)

### Note

Calibrated version includes calibration of the optical system only.

## Product Details

### Single Memory

This tachometer has an integrated optical transmitter and receiver at the top of the unit and a mechanical contact assembly at the base of the unit. The 5-digit LCD automatically inverts when switched from optical to contact so that the display is always the right way up when viewed.

Photo tachometer - direct reading rpm

Contact tachometer - direct reading, ranges rpm, m/min, ft/min

Memory recall of last reading



ENGLISH

## Specifications:

Best Accuracy	±0.05 %
Category	Contact, Optical
Battery Type	AA
Display Type	LCD
Dimensions	65 x 38 x 215mm
Height	215mm
Length	65mm
Maximum Speed	19999 rpm, 100000 rpm
Minimum Speed	0.5 rpm, 5 rpm
Model Number p	DT-2236
Width	38mm