

# Product Information



## UFR160x46-Ø20

EAN 4031582324686

Wheel centre made of Polyamide, Tread: elastic-tyre, non-marking, roller bearing

### Technical Data

Wheel diameter	160 mm
Width of Tread	46 mm
Axle Hole Ø	20 mm
Hub length	58 mm
Temperature	- 20 / + 80 °C
Standard	EN 12532
Weight	0.818 kg
Dynamic Load capacity	300 kg
Static Load capacity	600 kg
Hardness of tread	A 64 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

