

# LEDLENSER T<sup>2</sup> Professional

Ledlenser's handsome T<sup>2</sup> is a small fixed-focus torch that puts thrills before frills to competently out-shine many bigger rivals. It features a high-end CREE power LED that can beam a maximum 240 lumens up to 180 metres. On the end it has a single Dynamic Switch giving the user a simple choice of two light settings: Power for maximum brightness; or Low Power for prolonged battery life. Made from robust, aircraft-grade aluminium with secure grip and gold-plated internal battery contacts, it's the kind of torch professional tradesmen, security and emergency services personnel demand when they need a fast, dependable torch for robust everyday use. With a maximum burn time of 30 hours it's also one that will keep going when others have called it a day. Supplied with wrist strap and 3 x AAA batteries.

As a leading international brand of hand-held torches and head lamps, Ledlenser is renowned for superior German engineering, outstanding performance, and state-of-the-art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, Ledlenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. Ledlenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- Small fixed focus torch that out shines many larger torches
- Energy efficient Power LED Light Chip.
- State-of-the-art, reliable German engineering
- Dynamic Switch™ (Power/Low Power)
- Reflector lens for enhanced light optics
- Robust, yet lightweight aircraft-grade aluminium housing
- Frozen black coating
- Corrosion resistant gold-plated contacts for better conductivity
- Water and dust resistant. IPX4
- Supplied with: Wrist-strap and 3xAAA batteries

T2	BOOST	POWER	LOW POWER
POWER	x	240 lumens	25 lumens
BEAM DISTANCE	x	180 metres	60 metres
RUN TIME	x	4 hours	25 hours
SIZE	115x25mm	WEIGHT	98g

Supplied with : Wrist-strap and Duracell® batteries (3xAAA)



LEDLENSER T<sup>2</sup>

Code	Colour	Packaging	Barcode
9802	Black	Gift Box	4029113980203

**RRP ex.vat £36.62 / incl.vat £43.95**

**RRP ex.vat €39.23 / incl.vat €48.25**