

KYBKM-65HMU Stainless steel mini keyboard - Panel mount



Faceplate Dimensions(W X H): 300x110 mm

Basic Instructions

- Support Windows XP/Vista/7/8 and above, Linux and Unix
- comply with ISO/IEC 9995、GB/T14081 standard
- Keyboard made of high quality stainless steel
- With 65 customized keys
- Dustproof, waterproof, shake-proof and vandal proof

Applications:

- Check-in Kiosk, Info-Kiosk, Internet Kiosk, Medical Kiosk, Industrial Control Platform.

Interface: USB, PS/2 also available

Mechanism Performance

- Keyboard lifespan: more than 2 million
- Force on keys: 3-5N
- Key travel: >2.5mm

Environment adaptation

- Protection Level: IP65 static /IP54 dynamic
- Operating Temperature:
 1. Economical Grade: 0°C~+45°C RH:30~90%,
 2. Industrial Grade: -40°C~+60°C RH: 30~90%
- Storage temperature(Recommended): -25°C~+55°C RH:20~95%(No condensate)
- Maximum humidity in operating environment:90%
- Air Pressure: 60-106 Kpa

Approvals:

- RoHS,CE,FCC
- IP65,IK07