





LOC	DIST	REVISONS							
		P	LTR	DESCRIPTION			DATE	DWN	APVD
J	—		G1	REVISED ECR-07-017829			31AUG07	TS	KB



- △相手ハウジングと所定の機能を満たして嵌合できること。
△フードの反りは0.2以内。
3. 推奨取付けねじ: JIS B 1115 又は、1122 タッピンねじ
なべ1種、呼び径3を使用し締め付け後半田付けする。
(締め付けトルク: 0.4N・m 以下)
4. 適用製品規格: 108-5093
△[-A-] 面より2mmの範囲で測定のこと。
6. 相手ハウジングとの嵌合力は、29.4N以下
但し、リセタクルコンタクトは含まない。
- △IN COUPLING WITH THE PLUG HOUSING MATING SATISFIES FUNCTION.
△WARPAGE 0.2 MAX.
3. RECOMMENDED MOUNTING SCREW; 3mm DIA,
PAN HEAD, CLASS 1 TAPPING SCREW SPECIFIED IN JIS
B1115, B1122 (TORQUE: 0.4N・m MAX.)
4. PRODUCT SPECIFICATION; 108-5093
△TO BE MEASURED WITHIN 2mm FROM [-A-]
6. IN COUPLING WITH THE PLUG HOUSING MATING FORCE
29.4N MAX. WITHOUT REC CONTACTS.

	SEE CUSTOMER DRAWING 6-171362-1			6-171362-1
	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	2-5171362-1
	SELECTIVE-TIN (MATTE)	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-5171362-1
	PRE-TIN	PRE-TIN BRASS	NATURAL	4-171362-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD	GREEN	2-171362-4
	TIN-LEAD	SELECTIVE GOLD (0.76μm MIN.)	NATURAL	2-171362-1
OBSOLETE	TIN-LEAD	SELECTIVE GOLD	GREEN	1-171362-4
	TIN-LEAD	SELECTIVE GOLD (0.38μm MIN.)	NATURAL	1-171362-1
OBSOLETE	PRE-TIN	PRE-TIN BRASS	YELLOW	171362-7
OBSOLETE	PRE-TIN	PRE-TIN BRASS	GRAY	171362-6
OBSOLETE	PRE-TIN	PRE-TIN BRASS	BLUE	171362-5
	PRE-TIN	PRE-TIN BRASS	GREEN	171362-4
OBSOLETE	PRE-TIN	PRE-TIN BRASS	BROWN	171362-3
OBSOLETE	PRE-TIN	PRE-TIN BRASS	BLACK	171362-2
	PRE-TIN	PRE-TIN BRASS	NATURAL	171362-1
	SOLDERING SIDE 半田付け部	CONTACT SIDE 接触部側	COLOR 色	PART NUMBER 製品型番
	CONTACT FINISH コンタクト仕上			

一般公差 (GENERAL TOLERANCE)	
10mm以下	±0.2
30mm以下	±0.25
100mm以下	±0.3
角度	±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 特
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED

一般公差

0 PLC ±
1 PLC ±
2 PLC ±
3 PLC ±
4 PLC ±
ANGLES ±
FINISH
仕上

MATERIAL
材料

HOUSING: 66NYLON
TAB CONTACT: BRASS

DWN
T.SHINOHARA
18NOV05

CHK
K.BETSUI
18NOV05

APVD
K.BETSUI
18NOV05

PRODUCT SPEC
製品規格
SEE NOTE 4

APPLICATION SPEC
取付適用規格

WEIGHT
—

CUSTOMER DRAWING

Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME
名称
13POSITION VERTICAL TYPE CAP HOUSING ASSEMBLY
MULTI-INTERLOCK CONNECTOR. (WIRE TO P.C.BOARD)

SIZE
A2

CAGE CODE
00779

DRAWING NO
番号
171362

RESTRICTED TO

SCALE
尺度 2:1

SHEET
1 OF 1

REV
G1

AMP 1471-9 REV 31MAR2000