

Datasheet

RS Pro Spiral Wrap 1.5mm 10mm polyethylene (PE)

RS Stock No: **227-968**



Product Details

RS Pro spiral wrap in natural colour, is made of PE. It has internal diameter of 1.5 mm, maximum bundle diameter of 10 mm, maximum cable diameter of 3 mm, wall thickness of 0.5 mm and 5 m long. A pre-formed flexible PE spiral wrapping can be expanded by wrapping around cables forms, providing both protection and organisation of cables. Lead-outs allow cables to branch out at any point. A quick, effective system is capable of continuous adjustment or re-use. The operating temperature range is from -50 to +50 deg C.

Features and Benefits

- 5 m long
- Used for organising and protecting cables and hoses
- Easily applied to electrical harnesses, cables and wire bundles
- Flexible and durable
- Reusable
- Comes in natural colour
- Made from PE

**Specifications:**

Cable Diameter Range	1.5 to 10 mm
Colour	Natural
Internal Diameter	2 mm
Length	5 m
Material	PE
Maximum Cable Diameter	10 mm
Maximum Operating Temperature	+50°C
Minimum Cable Diameter	1.5 mm
Minimum Operating Temperature	-50°C
Operating Temperature Range	-50 to +50°C
Wall Thickness	0.5 mm
Outer Diameter	3 mm
Width	4.7 mm