

**Ordering number** C11613_ANNA-50-5-M

Family	Anna-50-5	FWHM	(simulated) 23
Type	Lens array	Efficiency	-
LED	Z5	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, glue		
Status	On production		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET
Anna-50-5 series
last update 4/4/2012



GENERAL INFORMATION

- Product series especially designed & optimized for Z5 series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:

http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>



Material: PMMA

- Versions:
 Anna-3-S
 Anna-3-M
 Anna-3-W
 Anna-4-S
 Anna-4-M
 Anna-4-W
 Anna-5-S
 Anna-5-M
 Anna-5-W
 Anna-6-S
 Anna-6-M
 Anna-6-W
 Anna-7-S
 Anna-7-M
 Anna-7-W

Number of cones varies;
 3, 4, 5, 6 and 7 pcs
 on bottom side depending
 the version.

This drawing is our property.
 It can't be reproduced
 or communicated without
 our written agreement.



L T F F e e i n

DRAWING TITLE
Datasheet Anna50-series Lens

DRAWN BY p	DATE 05.10.2010
CHECKED BY t k	DATE 03.08.2010
DESIGNED BY hh	DATE 30.07.2010

SIZE A4	DRAWING NUMBER -	REV 1
SCALE 1:1	WEIGHT (g)	SHEET 1/1

4

3

2

1

4

3

2

1

D

A