

NUMBER C-175778





METRIC


NEW 27.9

DIMENSIONS IN MILLIMETERS. DO NOT SCALE PRINT

PRINT COPY




CIRCUIT NO. 1
回路番号1側




- 注:
- 1. 材料: 66ナイロン (UL94V-0)
 - 2. 適用製品規格: 108-5297
 - 3. 取付適用規格: 114-5140


- NOTES,
- 1. MATERIAL: 66 NYLON (UL94V-0)
 - 2. PRODUCT SPEC.: 108-5297
 - 3. APPLICATION SPEC.: 114-5140



3 Pos. Only



2 Pos. Only



	7-175778-5	5-175778-5	3-175778-5	1-175778-5	15	28.0	30.8	32.0
7-	4	4	4	4	14	26.0	28.8	30.0
7-	3	3	3	3	13	24.0	26.8	28.0
7-	2	2	2	2	12	22.0	24.8	26.0
7-	1	1	1	1	11	20.0	22.8	24.0
7-	0	0	0	0	10	18.0	20.8	22.0
6-	9	4	2	9	9	16.0	18.8	20.0
6-	8	4	2	8	8	14.0	16.8	18.0
6-	7	4	2	7	7	12.0	14.8	16.0
6-	5	4	2	6	6	10.0	12.8	14.0
6-	5	4	2	5	5	8.0	10.8	12.0
6-	4	4	2	4	4	6.0	8.8	10.0
6-	3	4	2	3	3	4.0	6.8	8.0
6-175778-2	4-175778-2	2-175778-2	175778-2	2	2.0	4.8	6.0	
BLACK 黒色	YELLOW 黄色	BLUE 青色	NATURAL 自然色	Pos. 極数	A	B	C	

TE TE Connectivity

WIRE RANGE --- 22# (AWG) ---	INSULATION DIA --- 0.08 ---	NAME 圧着タイプ リセハウジング CRIMP TYPE RECEPTACLE HOUSING (AMP CT CONNECTOR 2mm PITCH)	
MATERIAL NOTE 注	FINISH ---	GENERAL TOLERANCE 0.05mm 10. ±0.2 10.0mm 30. ±0.25 30.0mm 100. ±0.3 ANGLES ±0.3°	SIZE LOC NUMBER A3 J C-175778
D2 ECO-11-005294 RK HMR DSAPR 11 DR. T. NAKAMURA 4/26/80 DE. T. NAKAMURA		SCALE 5-1	REV. D2 SHEET 1 OF 1
LTR REVISION RECORD DR CHK DA.E CHK. S. KIKUCHI 4/28/80 APP. S. Kikuchi			

CUSTOMER DRAWING