

77 42 115


Electronics Diagonal Cutter



- For fine cutting work, e.g. in electronics and fine mechanics
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened
- High-grade special tool steel, forged, multi stage oil-hardened
- Pointed head, without bevel
- Cutting edge hardness approx. 57 HRC



Article No.	77 42 115
EAN	4003773027997
Head	mirror polished
Handles	with multi-component grips
Style	4
Cutting capacities medium hard wire (diameter) Ø mm	0,8
Cutting capacities soft wire (diameter) Ø mm	0,3 - 1,3
D mm	7,5
B mm	14,0
A mm	11,0
Nominal size	115 mm
Length mm	115
Net weight g	80



technical change and errors excepted

