

AMP AMP Connect

MAIN MENU HELP
FAMILIES REGISTRATION

Alphabetical Picture Part Number
SEARCH SEARCH SEARCH

Go To Step Search™ Screen

206036-2 -- 1 of 1 products

**CPC (Circular Plastic) & Metal-Shell CPC Connectors
CPC Connectors**

General **INFO**

Sales **INFO**

Customer Drawings
SPECIFICATIONS

CAD Geometry

CPC Connectors, Series 3



Line art represents typical product only.

-  [Line Art](#)
-  [Contact Arrangement](#)
-  [Panel Cutout](#)

Searchable Features:

Product Type	Connector
# of Positions	3
Sex	Receptacle
Preloaded	No
Pin/Socket	Pin
Terminate To	Wire
Shell Size	17
Shell Type	All Plastic
Shell Thread Size	15/16-20 UNEF-2A
Numbering	Standard
Product Series	Series III
Panel Attachment	Yes
Panel Hole Type	Mounting Holes
Sealed	Yes
VDE Tested	No

Other Properties:

Dim. A	1.635 [41.53] in. [mm]
Dim. B	.420 [10.67] in. [mm]
Dim. C	.094 [2.39] in. [mm]
Dim. D	1.050 [26.67] in. [mm]
Dim. E	1.110 [28.19] in. [mm]
Dim. F	1.125 [28.58] in. [mm]
Dim. G	1.435 [36.45] in. [mm]
Dim. H	.150 [3.81] in. [mm]
Dim. J	1.210 [30.73] in. [mm]
Wire Insulation Diameter	.220 [5.59] in. [mm]
Panel Attachment Method	Square Flange
Housing Material	Thermoplastic
Housing Material Flammability Rating	UL 94V-0
Housing Color	Black