

3125BS6W



Products Low Voltage Products and Systems Industrial Plugs and Sockets Plugs & Sockets Surface Inlets

General Information

Extended Product Type:	3125BS6W
Product ID:	2CMA167282R1000
EAN:	7392696672825
Catalog Description:	Surface inlet, 6h, 125A, IP67, 3P+E
Long Description:	Surface Inlet, earthing sleeve position 6h, rated current 125A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

Additional Information

Additional Information:	3P+E
Cable Cross-Section:	16 ... 70 mm ²
Cable Entry Position:	Cable entry Ø50mm
Color:	Red
Country of Origin:	Czech Republic (CZ)
Customs Tariff Number:	85366990
Data Sheet, Technical Information:	2CMC700014C0008
Declaration:	2CMC700005D0001
Declaration of Conformity - CE:	2CMC700005D0001
Degree of Protection:	IP67 / IP69
E-nummer:	2417279
EAN:	7392696672825
ETIM 4:	EC001319 - CEE plug for mounting on machines and equipment
ETIM 5:	EC000140 - CEE plug
ETIM 6:	EC000140 - CEE plug
Enclosure Material:	Thermoplastic polyester (PBT)
Environmental Information:	2CMC700001D0002
Frequency (f):	60 Hz
Function:	Surface inlet
Gross Weight:	4.1 kg
Housing Material:	Thermoplastic (PBT)
IIT Publishing Status:	Level 0 - Information enabled
Instructions and Manuals:	2CMC700002D0001
Invoice Description:	Ind. P&S#3125BS6W
Minimum Order Quantity:	1 piece
Number of Poles:	4
Object Classification Code:	2CMT005069
Package Level 1 EAN:	7392696672825
Package Level 1 Gross Weight:	4.1 kg
Package Level 1 Height:	378 mm
Package Level 1 Length:	182 mm
Package Level 1 Units:	1 piece
Package Level 1 Width:	154 mm
Product Main Type:	TBS
Product Name:	Industrial Surface Inlet
Product Net Depth:	265 mm
Product Net Height:	265 mm

Product Net Length:	160 mm
Product Net Weight:	4.1 kg
Product Net Width:	145 mm
Protection Type:	Watertight
Rated Current (I_n):	125 A
Rated Voltage (U_r):	380 ... 415 V
RoHS Date:	L23
RoHS Information:	2CMC700057D0001
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01
Selling Unit of Measure:	piece
Short Description:	Surface inlet, 6h, 125A, IP67, 3P+E
Size:	274X145X160
Standards:	IEC 60309-1 IEC 60309-2
Suitable For:	Surface Inlets
Suitable for Product Class:	Industrial Plugs and Sockets
UNSPSC:	39120000
Clock Position Of Grounding Contact:	6 hour

