

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	DWN
			H2	REVISED PER ECR-08-022232	06OCT08	APVD

AMP
WIRE RANGE

4 AWG
SOLID OR STRANDED

- 1
- STAMP AMP 4W* APPROX AS SHOWN

2


3

4

5


6

7



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS		MAX RECOMMENDED OPERATING TEMPERATURE: 170° C
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752	VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111	CIRCULAR MIL AREA: 16.8-26.7mm²[33,100-52,600] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

6 7	20	LOOSE PIECE, BOX	4	8-34320-5
---	----	LOOSE PIECE	5	34320-1
6 7	----	LOOSE PIECE	4	34320
APPROVALS	QTY	PACKAGE TYPE	FINISH	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TA BRINKMAN 4-14-93		 Tyco Electronics Corporation Harrisburg, PA 17105-3608		
DIMENSIONS: INCHES		CHK DA PATTERSON 4-14-93				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD DA PATTERSON 4-14-93		NAME SPLICE, PARALLEL, SOLISTRAND		
		PRODUCT SPEC —				
		APPLICATION SPEC —				
		—				
MATERIAL 	FINISH SEE TABLE	WEIGHT —	SIZE A2	CAGE CODE 00779	DRAWING NO C=34320	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 10:1		SHEET 1 of 1	REV H2