




NOTES:

1. MATERIAL

- 1.1 HDMI CABLE: (7/0.10TC*1P+7/0.10TC+FAM)*4PCS+7/0.12TC*3C+7/0.12TC*1P+AL+7/0.12TC+128/0.12ALM+BLACK PVC JACKET.
OD: $\varnothing 6.0 \pm 0.2$ mm
- 1.2 HDMI 19PIN TYPE A MALE : BLACK INSULATION, GOLD PLATED CONTACTS, NICKEL PLATED SHELL.
- 1.3 DVI(18+1) MALE: BLACK INSULATION, GOLD PLATED CONTACTS G/F, NICKEL PLATED SHELL.
- 1.4 THUMB SCREW TO BE MOLDED BLACK PVC. NICKEL PLATED SCREW.
- 1.5 ALL HOOD: MOLDED BLACK PVC.

2. ELECTRICAL

- 2.1 100% OPEN AND SHORT TEST.
- 2.2 CONDUCTOR RESISTANCE: 5 OHMS MAX.
- 2.3 INSULATION RESISTANCE: 10 MEGOHMS MIN.
- 2.4 HI-POT: DC300V/0.01S.

3. PACKAGING: A PC/PE-BAG PACKAGING .

4. ALL MATERIALS ARE REACH COMPLIANT.

P/N	L(mm)
11.99.5519	1000±30mm
11.99.5522	2000±50mm
11.99.5532	3000±70mm
11.99.5552	5000±70mm

PIN OUT			
P1		P2	
1		2 BLUE	} RED FAM
3		1 WHITE	
2		3 DRAIN	
4		10 BLUE	} SILVER FAM
6		9 WHITE	
5		11 DRAIN	
7		18 BLUE	} BLUE FAM
9		17 WHITE	
8		19 DRAIN	
10		23 BLUE	} BROWN FAM
12		24 WHITE	
11		22 DRAIN	
15		6 RED	
16		7 WHITE	
17		15 YELLOW	
18		14 ORANGE	
19		16 PURPLE	
SHELL	DRAIN	SHELL	



REV.			LENGTH TOLERANCE:	SCALE:	PAGE:		ENG:
02	ADD THE ONE	2012-01-05	X. ± 0.5	FREE	1/1		
01	CHANGE THE CABLE MARKING	2011-02-23	.X ± 0.2	UNIT:			CHECKED:
00	NEW ISSUE	2010-03-16	.XX ± 0.1	mm	VALUE DVI Cable, DVI M-HDMI M, black		
	MODIFY DESCRIPTION	DATE	ANGLE TOLERANCE:	VERSION:			APPROVED:
			X' $\pm 3^\circ$	02			
			X' $\pm 1^\circ$				