





TOLERANCES (UNLESS SPECIFIED)	
0-10mm	±0.2mm
10.1-50mm	±0.5mm
50.1-250mm	±1.0mm
>250mm	±2.0mm



PORTABLE TOOLS TRANSFORMER
 TYPE: ISOLATION TRANSFORMER
 INPUT: 230V, 50Hz
 OUTPUT: 55V-0-55V
 CENTRE TAPPED TO EARTH
 INTERMITTENT RATING: 4000VA
 5 MINS ON, 15 MINS OFF
 CONTINUOUS RATING: 2000VA
 THERMAL CUT-OUT: 15A
 OUTPUT SOCKET: 2x 16A BS EN 60309
 RATED IP44
 ENCLOSURE: GRP
 RATED IP55
 COLOUR: YELLOW

REV	4		CARROLL & MEYNELL TRANSFORMERS LIMITED TEL: 01642 617406 FAX: 01642 614178 enquiries@carroll-meynell.com	TITLE	DRAWN	PROJECTION	DATE	SCALE	
	3			CM40002	SH			NTS	
	2			RS CODE 260-4301	DRAW No			REV	PAGE
	1	RATING, GB 14/12/11		ALL DIMENSIONS IN mm	3264		1	1/1	