

## Decorative Vintage Candle

Decorative Vintage Candle 40W 230/240V E27 SV1

**0023878**



### Range Features

- 

## PRODUCT OVERVIEW

|                            |               |
|----------------------------|---------------|
| Lamp finish                | Coloured      |
| Lamp shape                 | Candle        |
| Colour temperature (K)     | 2100          |
| CRI (Ra)                   | 100           |
| Dimmable                   | Yes           |
| EAN code                   | 5410288238784 |
| Energy class               | E             |
| Cap/Base                   | E27           |
| Watt (Nominal) (W)         | 40            |
| Ordering number            | 0023878       |
| Average life (Rated) (h)   | 2000          |
| Luminous flux (Rated) (lm) | 200           |
| Technology                 | Incandescent  |
| Voltage (V)                | 230-240       |

## DATA TABLE

### General data

|                            |                |
|----------------------------|----------------|
| Average life (Nominal) (h) | 2000           |
| Control gear required      | No             |
| Lamp finish                | Coloured       |
| Lamp shape                 | Candle         |
| Dimmable                   | Yes            |
| EAN code                   | 5410288238784  |
| Energy class               | E              |
| Energy saving lamp         | No             |
| General application        | Hospitality    |
| Intended purpose           | Decor Lighting |
| Cap/Base                   | E27            |
| Lamp mercury content (mg)  | 0              |

## Decorative Vintage Candle

*Decorative Vintage Candle 40W 230/240V E27 SV1*

**0023878**

|  |  |
|--|--|
| <b>Ordering number</b>                             | 0023878  |
| <b>Product name</b>                                | Decorative Vintage Candle 40W 230/240V E27 SV1 |
| <b>Average life (Rated) (h)</b>                    | 2000   |
| <b>Special purpose lamp</b>                        | Yes  |
| <b>Starting time (max) (s)</b>                     | 0.01   |
| <b>Technology</b>                                  | Incandescent                                   |
| <b>Transformer required</b>                        | No   |
| <b>Warm-up time to 60% of full light (max) (s)</b> | Instant full light                             |

### Optical data

|                                     |      |
|-------------------------------------|------|
| <b>Colour temperature (K)</b>       | 2100 |
| <b>CRI (Ra)</b>                     | 100  |
| <b>Luminous flux (Nominal) (lm)</b> | 200  |
| <b>Luminous flux (Rated) (lm)</b>   | 200  |
| <b>Suitable for accent lighting</b> | No   |

### Electrical data

|  |         |
|--|---------|
| <b>kWh per 1000 hours burning time</b> | 40      |
| <b>Lamp power factor</b>               | 1       |
| <b>Watt (Nominal) (W)</b>              | 40      |
| <b>Watt (Rated) (W)</b>                | 40      |
| <b>Voltage (V)</b>                     | 230-240 |

### Physical data

|                                    |    |
|------------------------------------|----|
| <b>Max. Lamp Diameter (mm) - D</b> | 35 |
| <b>Lamp Length (mm) - C/L</b>      | 98 |

## Decorative Vintage Candle

Decorative Vintage Candle 40W 230/240V E27 SV1

**0023878**

