




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
FT	0	P	LTR	DESCRIPTION	DATE
		C		REVISED PER 0G3B-0092-05	1/27/05



RECOMMENDED PANEL CUTOUT

1. HOUSING, ADAPTER AND PRESSURE PLATE: NYLON, BLACK.
WIRE ENTRY SEAL: ELASTOMER, SEE TABLE.
PERIPHERAL SEAL: ELASTOMER, GREY.

2. CONNECTOR WILL ACCEPT (16) MULTIMATE PIN CONTACTS.

W/ 4-40 THREADED INSERT	RED-IRON OXIDE	.065 — .120	STANDARD	796275-3
3.18 ± 0.07 [0.150 ± 0.003]	YELLOW	.040 — .080	SMALL	796275-2
3.18 ± 0.07 [0.150 ± 0.003]	RED-IRON OXIDE	.065 — .120	STANDARD	796275-1
H	SEAL COLOR	DIA. RANGE	INSULATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. McEACHIN 27-JAN-2000	tyco Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: mm [INCHES]		CHK K. DOWHOWER 27-JAN-2000		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD K. DOWHOWER 27-JAN-2000	NAME ASSEMBLY, RECEPTACLE, STANDARD SEX, 17-16, STANDARD OR SMALL INSULATION DIA., SEALED	
0 PLC ± -		PRODUCT SPEC -		
1 PLC ± -		APPLICATION SPEC -	SIZE A2 CAGE CODE 00779 DRAWING NO C=796275	
2 PLC ± -		WEIGHT -		
3 PLC ± -		CUSTOMER DRAWING	SCALE 2:1	SHEET 1 OF 1
4 PLC ± -				REV C
ANGLES ± -				
FINISH -				