



Sample photo

Order symbol: AL 123608
Product nbr: 7011250
Description: Enclosure
Remarks: Aluminium

EAN: 6418074004178
El. number:
Finland: 3423621
Denmark: 8212004728
Italy: 7321060
Sweden: 2536323

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and stainless steel cover screws.

Dimensions:				Rating:	
mm:	362	125	81	Ingress Protection (EN 60529): IP 66/67	
inch:	14.3	4.9	3.2	Impact Resistance (EN 62262): IK 08	
Materials:				NEMA Class: NEMA 1, 4, 4X, 12, 13	
Material:	Aluminium			Certificates: Underwriters Laboratories Fimko UL Canada Gost R	
Base colour:	RAL 7001				
Cover colour:	RAL 7001				
Cover screws material:	Stainless steel				
Gasket material:	Polyurethane				
Temperatures:					
Short term:	-50 ... 140 °C				
Continuous:	-50 ... 80 °C				
Short term:	-60 ... 285 °F				
Continuous:	-60 ... 175 °F				
Accessories:					
AM 1212	Mounting plate				
AM 1222	Mounting plate				
AM 1236	Mounting plate				
ARH 12	DIN-35 Mounting rail				
ARH 36	DIN-35 Mounting rail				
MR 75005	Selftapping taptite screw M5				
MRS 28541	Wall fastening lug (2 pcs)				
PH A & AH A/B	Hinge set				

