

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

—, —

© COPYRIGHT — BY TYCO ELECTRONICS CORPORATION.

ALL INTERNATIONAL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

H

—

C

H-9720

21-04-92

S.M.

—

D

EH-0054-92

07-12-92

D.K.

—

J

ECR-09-000314

21-05-09

AEG

KMA

5,0 HEX

GROOVE TO INDICATE M3 INNER THREAD

10,8	4-40 UNC	4-40 UNC	6,0	TINPLATED	BRASS	3-829261-0
9,8	M3	4-40 UNC	5,0			2-829261-8
	4-40 UNC	M3	5,0			2-829261-6
	M3	M3	5,0			2-829261-4
	4-40 UNC	4-40 UNC	5,0			2-829261-2
19,0	M3	4-40 UNC	14,2	1-829261-8		
	4-40 UNC	M3	14,2	1-829261-6		
	M3	M3	14,2	1-829261-4		
	4-40 UNC	4-40 UNC	14,2	1-829261-2		
12,7	M3	4-40 UNC	7,9	829261-8		
	4-40 UNC	M3	7,9	829261-6		
	M3	M3	7,9	829261-4		
	4-40 UNC	4-40 UNC	7,9	829261-2		
DIM "D"	DIM "C"	DIM "B"	DIM "A"	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± 0,2

2 PLC ± —

3 PLC ± —

4 PLC ± —

ANGLES ±

MATERIAL

—

FINISH

—

DWN

D.KESSLER

02APR91

CHK

C.V.TILBURG

23APR91

APVD

L.V.SOEST

25APR91

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

Tyco Electronics Corporation

's-Hertogenbosch, Nederland

NAME

SCREWLOCK, FEMALE HD-SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-829261

—

SCALE

NTS

SHEET

1 OF 1

REV

J

1470-19 (1/08)