



Main

Range of product	Canalis
Range compatibility	Canalis KN
Product or component type	Tap-off unit
Busbar trunking compatibility	Canalis KN busbar trunking with plug-in outlets
[Ie] rated operational current	32 A
Protection type	Circuit breaker : miniature circuit breaker (MCB)
Mounting mode	Plug-in with fixed polarity
Tap-off unit polarity	3L+N+PE
Colour	White RAL 9001

Complementary

Device application	Low power distribution
Provided equipment	Blanking plate Circuit breaker to be ordered separately
[Ue] rated operational voltage	230...500 V depending on protective device
[Uimp] rated impulse withstand voltage	4.6 kV
[Ui] rated insulation voltage	400 V depending on protective device 500 V depending on protective device
Network frequency	50/60 Hz
Electrical connection	Pre-wired terminal block - ISO32 - cable : 6 mm ² flexible Pre-wired terminal block - ISO32 - cable : 10 mm ² rigid
Door/Cover opening side	Front
Tap-off unit disconnection mode	By drawing out
Standards	IEC 61439-1 IEC 61439-6
18 mm pitches	5
Width	135 mm
Depth	95 mm

Height	165 mm
Product weight	0.6 kg

Environment

Earthing system	TT IT TN-S
IP degree of protection	IP55 conforming to IEC 60529
IK degree of protection	IK08 conforming to IEC 62262

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1012 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------