

PSZROX-0625 - PSZROX

General Part Information

Product Description		PSZROX-0625
Article Number		33360
POPNut Type	i	PSZROX
Standard Bulk Pack Quantity		4,000

Geometry / Dimensions

Thread Size		M6
Body Type (open / closed)	i	Open
Body Features	i	Round
Body Length (mm)		14.80
Min. Grip Thickness (mm)		0.80
Max. Grip Thickness (mm)		2.50
Head Style	i	Reduced Head
Hole Diameter (mm)		9.60
Head Diameter (mm)		10.50
Head Thickness (mm)		0.90
Barrel Diameter (mm)		9.50

Material / Weight

Material	i	Steel
Weight per thousand (kg)		3.4

