

Datasheet

RS Pro Right Angle 50Ω Cable Mount BNC Connector Plug, Clamp Termination RG174B Silver

RS Stock No: **546-4370**



Product Details

RS Pro right angle cable mount BNC connector plug features silver body plating and copper contacts. This male connector plug has 50 Ω impedance. It operates at a voltage rating of 335 V and temperature rating of -65 to +85°C.

Features and Benefits

- Silver body plating and copper contacts
- Clamp termination method
- Male connector



ENGLISH

Specifications:

Body Orientation	Right Angle
Body Plating	Silver
Cable Type	RG174B
Contact Material	Copper
Gender	Male
Impedance	50 Ω
Mounting Type	Cable Mount
Polarity	Normal
Termination Method	Clamp
Standards Met	RoHS Compliant