

BMP71 BradyBondz™ Labels



BradyBondz™ Labels for the BMP71 Label Printer. Please Note: This material is UL, CSA & AGA approved with its respective ribbon. See the "Recommended Ribbon Series" for the appropriate ribbon to use.

[Overview](#) [Specifications](#)

Article Number: 114962
Order Reference: M71-30-423-TEST
Size - Width (mm): 38.1
Size - Height (mm): 19.05
Finish: Gloss
Colour: Green on White
Material Type: Permanent Polyester
Brady Material Number: [B-423](#)
Adhesive: Permanent Acrylic
Approval/Compliance: AGA Approved, CSA Approved, Halogen-Free (DIN VDE 0472/parts 815), UL Recognised
Max. Service Temp. °C: 110
Through Hole Technology: Top: Yes. In extreme high temperatures, testing of this material is recommended, Bottom: No
Surface Mount Technology SMT: No, this material does not work with this application
After Process: Yes, this material will work with this application
Board Application: Through Hole - Top
QTY. per Row: 1
Printer Compatibility: BMP71
Industry: Manufacturing
Application(s): Circuit Board Identification, General & Industrial Identification, Through Hole - Top