

## General Information

|                        |                                                                                                                              |
|------------------------|------------------------------------------------------------------------------------------------------------------------------|
| Extended Product Type: | 416-P6                                                                                                                       |
| Product ID:            | 2CMA193511R1000                                                                                                              |
| EAN:                   | 7392696935111                                                                                                                |
| Catalog Description:   | Plug, 6h, 16A, IP44, 3P+N+E                                                                                                  |
| Long Description:      | Plug, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, 50 - 60 Hertz, color code red |

## Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Plugs

## Ordering

|                         |                     |
|-------------------------|---------------------|
| EAN:                    | 7392696935111       |
| Minimum Order Quantity: | 10 piece            |
| Country of Origin:      | Czech Republic (CZ) |

## Dimensions

|                     |          |
|---------------------|----------|
| Product Net Width:  | 73 mm    |
| Product Net Height: | 73 mm    |
| Product Net Length: | 142 mm   |
| Product Net Depth:  | 73 mm    |
| Product Net Weight: | 0.174 kg |

## Container Information

|                               |               |
|-------------------------------|---------------|
| Package Level 1 Width:        | 158 mm        |
| Package Level 1 Length:       | 138 mm        |
| Package Level 1 Height:       | 345 mm        |
| Package Level 1 Gross Weight: | 0.174 kg      |
| Package Level 1 EAN:          | 7392696935111 |
| Package Level 1 Units:        | 10 piece      |

## Environmental

|              |                                                                                          |
|--------------|------------------------------------------------------------------------------------------|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01 |
|--------------|------------------------------------------------------------------------------------------|

## Certificates and Declarations (Document Number)

|                                 |                 |
|---------------------------------|-----------------|
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Environmental Information:      | 2CMC700001D0002 |
| RoHS Information:               | 2CMC700057D0001 |

## Additional Information

|                                  |                                |
|----------------------------------|--------------------------------|
| Additional Information:          | Cable entry, compression gland |
| Cable Cross-Section:             | 1.0 ... 2.5 mm <sup>2</sup>    |
| Color:                           | Red                            |
| Degree of Protection:            | IP44                           |
| Enclosure Material:              | Polyamide                      |
| Frequency (f):                   | 50 Hz                          |
| Function:                        | Plug                           |
| IIT Publishing Status:           | Level 0 - Information enabled  |
| Invoice Description:             | Ind. P&S#416-P6                |
| Number of Poles:                 | 5                              |
| Object Classification Code:      | 2CMT005069                     |
| Product Main Type:               | P                              |
| Product Name:                    | Industrial Plug                |
| Protection Type:                 | Splashproof                    |
| Rated Current (I <sub>n</sub> ): | 16 A                           |
| Rated Voltage (U <sub>r</sub> ): | 346 ... 415 V                  |
| RoHS Date:                       | L23                            |
| Standards:                       | IEC 60309-1,-2                 |
| Suitable For:                    | Plugs                          |
| Suitable for Product Class:      | Industrial Plugs and Sockets   |

**Classifications**

|           |          |
|-----------|----------|
| E-nummer: | 2416170  |
| UNSPSC:   | 39120000 |

