



Security Tech Germany

41/40mm ETERNA Laminated Steel Padlocks

- Individually plated laminated steel : Up to 40 years weather protection
- Pin tumbler cylinder with anti-pick mushroom pins : Resists picking
- Hardened steel shackle on 30mm : Through hardened steel alloy 40mm & above
- Keyed to differ (KD) plus numerous KA/MK suites available : Multiple site security
- Long shackle (HB) versions available : For most security needs
- Hardened keyway protection : Resists drilling & pulling attacks



Made in Germany Paracentric Keyway Drill Resistant Saw Resistant Double Bolted Keyed Alike Available



Master keyed Available 10mm Bitted Available



41/40 Laminated Padlock with 100/100 Hasp & Staple

At last a laminated steel padlock that does not rust Eterna plating - another strength & corrosion solution from ABUS

- Each laminated steel plate is individually coated in the new ETERNA treatment process
- ETERNA treatment offers 13 times more corrosion protection than normal zinc plating
- Salt bath tests give the equivalent of 40 years of weather protection
- 180 hours in a salt water bath will kill most padlocks, but not the new 41 ETERNA - it worked perfectly

RH4/5 Keying System

RH 4/5 Keying system allows a whole range of ABUS padlocks to be incorporated in a single Keyed Alike (KA) or Master Keyed (MK) suite

Padlocks can be supplied assembled or keyed by locksmiths to their exact requirements



41/40

Keyed Alike version available
- ex stock

Other Keyed Alike & Master Keyed versions available
to special order

ABUS UK Product Reference	ABUS Code	ABUS GPS	mm	mm	mm	mm	mm	mm	Weight gms	Key Blank	
										Reference	Code
41/40 Laminated Padlock	06371	6	18.5	20	7	44	63	26	214	RH4	02706
41/40KA EE0022 Laminated Padlock	33742	6	18.5	20	7	44	63	26	214	RH4	02706