

50/60 Hz CURRENT TRANSFORMERS FOR PCB MOUNTING

SERIES 620X



All dimensions are in mm
Linear dimensional tolerance ± 0.2 mm

FEATURES

- Current range from 1 - 100 A · Frequency 50/60 Hz
- Fully encapsulated
- Primary to secondary insulation 2.5 kV AC
- Operating temperature range: -40°C to $+120^{\circ}\text{C}$
- Place of manufacture is certified according to ISO 9001:2008 / 14001:2004
- Fully RoHS compliant
- More details on request or in the single data sheets

Part Number	Current Range [A]	Output Voltage @ $I_{\max}$ Tolerance $\pm 10\%$	Load Resistant [Ω]	Picture Number
L01-6200	1-10	33.3mV	50	1
L01-6201	1-20	58.3 mV	50	2
L01-6202	1-30	55 mV	220	3
L01-6203	5-50	100 mV	220	4
L01-6204	5-75	119.5 mV	220	4
L01-6205	5-100	128 mV	220	4

