

ELECTRONIC TRANSFORMERS

For low voltage halogen lamps

150WATT VERSION

Internationally approved, high quality electronic transformers

Features

- Short circuit protection
- Overload protection
- Over temperature protection
- Dimmable
- TUV approved and certified
- CE marked

CHARACTERISTICS:

Power: 50-150W

Terminal blocks connections

Input voltage: 220-240V/50Hz (240V nominal for UK)

Input current: 0.35A at 80W

Output voltage: 11.6V~eff

Power factor: 0.99

Ambient temperature Ta: Max. 50 degrees Celsius

Case temperature Tc: Max. 70 degrees Celsius

Tested in accordance with:

EN55015, EN61000, EN61046, EN61547

Input terminals: 2 groups

Output terminals: 3 groups

Dimmable with phase lagging dimmers



Part No.	Size (lwxh)	Input	Output	Termination	Case type
ET150	214x47x38	230v	11.6v	Terminals	Standard

