

Device marker - US-EMSP (50X30) - 0828786

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Device marker, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Screws, rivets, Lettering field: 50 x 30 mm




The figure shows the US-EMSP (75,6x54) version

Why buy this product

- ✓ The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- ✓ The US-EMSP ... UniSheet labeling range includes markers that can be attached using screws or rivets
- ✓ The perforated markers are easy to separate and can be easily fitted
- ✓ Labeling service: Phoenix Contact can custom-label all UniSheet markers according to your requirements
- ✓ The sheets provide space for including function texts

Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 559652 |
| Weight per Piece (excluding packing) | 14.53 g |
| Custom tariff number | 39204910 |
| Country of origin | Germany |

Technical data

Dimensions

| | |
|---------------|---------|
| Length (b) | 59.7 mm |
| Height | 0.5 mm |
| Width (a) | 29.8 mm |
| Hole diameter | 3.20 mm |

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -30 °C ... 80 °C |
|---------------------------------|------------------|

General

| | |
|---|---------------|
| Color | white |
| Components | Silicone-free |
| Inflammability class according to UL 94 | V0 |

Device marker - US-EMSP (50X30) - 0828786

Technical data

General

| | |
|-------------------------------------|-----------------------------|
| Material | PVC |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 4 |
| Number of individual labels per row | 1 |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451



Magazine for the THERMOMARK CARD printer, for accommodating US cards

