





| LOC<br>J | DIST<br>— | REVISIONS |     |                           |         |     |      |
|----------|-----------|-----------|-----|---------------------------|---------|-----|------|
|          |           | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
|          |           |           | E3  | REVISED PER ECO—11—005030 | 11MAR11 | RK  | HMR  |




|                             |           |                   |
|-----------------------------|-----------|-------------------|
|                             | XX        | 1-179555-8        |
|                             | XY        | 3-179555-6        |
|                             | YY        | 2-179555-6        |
|                             | XX        | 1-179555-6        |
|                             | ZZ        | 4-179555-3        |
|                             | XY        | 3-179555-3        |
|                             | YY        | 2-179555-3        |
|                             | XX        | 1-179555-3        |
| キーイングパターン<br>KEYING PATTERN | キー<br>KEY | 型番<br>PART NUMBER |

- 1 MATERIAL:GLASS FILLED THERMO PLASTIC, POLYESTER  
COLOR:BLACK
- 2 PANEL ATTACHMENT RECOMMENDATION M3 SCREW

- 1 材料:ガラス入り熱可塑性ポリエステル樹脂 色:黒
- 2 パネル取付推奨ネジ M3

|              |       |    |       |       |    |      |   |       |   |                   |
|--------------|-------|----|-------|-------|----|------|---|-------|---|-------------------|
| 20           | 78.23 | 70 | 59.72 | 52.72 | 61 | 18.4 | 4 | 45.72 | 9 | 1-179555-8        |
| 12           | 57.91 | 49 | 39.40 | 32.40 | 41 | 18.4 | 4 | 25.40 | 5 | 3-179555-6        |
| 12           | 57.91 | 49 | 39.40 | 32.40 | 41 | 18.4 | 4 | 25.40 | 5 | 2-179555-6        |
| 12           | 57.91 | 49 | 39.40 | 32.40 | 41 | 18.4 | 4 | 25.40 | 5 | 1-179555-6        |
| 6            | 41.91 | 33 | 24.16 | 17.00 | 25 | 8.4  | 2 | 10.16 | 2 | 4-179555-3        |
| 6            | 41.91 | 33 | 24.16 | 17.16 | 25 | 8.4  | 2 | 10.16 | 2 | 3-179555-3        |
| 6            | 41.91 | 33 | 24.16 | 17.16 | 25 | 8.4  | 2 | 10.16 | 2 | 2-179555-3        |
| 6            | 41.91 | 33 | 24.16 | 17.16 | 25 | 8.4  | 2 | 10.16 | 2 | 1-179555-3        |
| 極数<br>POS.   | A     | B  | C     | D     | E  | F    | G | H     | N | 型番<br>PART NUMBER |
| 寸法 DIMENSION |       |    |       |       |    |      |   |       |   |                   |



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm

MATERIAL  
1

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0-PLC 10 ± 0.2  
1-PLC 10< 30 ± 0.25  
2-PLC 30< ± 0.3  
3-PLC ±  
4-PLC ±  
ANGLES ± 3°  
FINISH

DWN N.MATSUBARA 31JAN1994  
CHK S.MANABE 1FEB1994  
APVD S.MANABE 1FEB1994  
PRODUCT SPEC  
108-5349  
APPLICATION SPEC  
114-5148  
WEIGHT  
CUSTOMER DRAWING

STE TE Connectivity

NAME  
パネルマウントタイプ タブハウジング ダイナミック 3200シリーズ  
WIRE TO WIRE TAB HSG FOR DYNAMIC D-3200M  
PANEL MOUNT TYPE

SIZE A3  
CAGE CODE 00779  
DRAWING NO C-179555  
RESTRICTED TO  
SCALE 2:1  
SHEET 1 OF 1  
REV E3