

Datasheet

Stock No: 775-6084

RS Pro 2 Core Black 2192Y Mains Power Cable



Code

H03VVH2-F CU/PVC/PVC

CU: IEC 60228 CLASS 5

F: Flexible conductor

Standards

TS 9760 HD 21.5.S3-VDE 0281-5-IEC60227-5

Technical Data

Max. operating temperature : 70 °C

Short circuit temperature : 160 °C (max. 5 sn.)

Rated voltage : 300/300V

Application

Used on household appliances in covered, dry, steamed and humid areas where low mechanical stress exists.

Construction

1. Flexible wires with fine stranded copper conductors
2. PVC insulation.
3. PVC sheath

BOYUT VE AĞIRLIKLAR (DIMENSIONS AND WEIGHTS)				ELEKTRİKSEL ÖZELLİKLER (ELECTRICAL PROPERTIES)	
Type Tip	Nominal Kesit Nominal cross- section	Dış Çap(yaklaşık) Overall Diameter (approx.)	Net Ağırlık(yaklaşık) Net Weight(apprx.)	İletken DC Direnci 20 °C'de max. DC Conductor Resistance at 20 °C	Akım taşıma kapasitesi Current Carrying Capacity
	mm ²	mm	kg/km	ohm / km	Havada 30 °C'de In Air at 30 °C
H03VVH2-F	2X0,50	3,36x5,34	29,44	39	3
	2X0,75	3,7x5,76	36,81	26	6

