



ENGLISH

Datasheet

RS Pro 5.08mm Pitch Straight PCB Terminal Block with Screw Termination, Through Hole, 2 Way

RS Stock No: **790-1168**



Product Details

RS Pro 5.08 mm pitch straight PCB terminal block features screw termination and through hole mounting type. This 2-way terminal block has rectangular Tin plated PC tails which are 1.0 x 0.8 mm by 3.5 mm long. This terminal block is suitable for 12-26 AWG wire and it comes with slotted head screws.

**Specifications:**

Body Orientation	Straight
Colour	Green
Current Rating	16 A
Depth	14 mm
Gender	Female
Length	10.16 mm
Material	Nylon 66
Mounting Type	Through Hole
Number of Contacts	2
Number of Rows	1
Pitch	5.08 mm
Termination Method	Screw
Type	PCB Terminal Block
Voltage Rating	300 V
Width	10.2 mm
Insulation Resistance	>2000 mΩ
American Wire Gauge	12 to 26 AWG
Insulation Withstand Voltage	2000 V ac
Operating Temperature Range	-40 to +105°C
Flammability Rating	UL 94 V-0