

## Sleeve frame - VC-TR1/2M - 1852891

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve frame, without PE, for contact insert modules, type 1, number of insert modules 2



### Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 5 pc                                                                                                    |
| Minimum order quantity               | 5 pc                                                                                                    |
| GTIN                                 | <br>4 017918 133757 |
| Weight per Piece (excluding packing) | 8.44 g                                                                                                  |
| Custom tariff number                 | 85389099                                                                                                |
| Country of origin                    | Poland                                                                                                  |

### Technical data

#### Dimensions

|        |         |
|--------|---------|
| Height | 27.5 mm |
| Width  | 50.2 mm |

#### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

#### General

|                                         |         |
|-----------------------------------------|---------|
| Type                                    | VC1     |
| Color                                   | black   |
| Material                                | PA-GF   |
| Housing material                        | Plastic |
| Inflammability class according to UL 94 | V0      |

### Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
|------------|----------|

## Sleeve frame - VC-TR1/2M - 1852891

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27189239 |
| eCl@ss 5.1 | 27189239 |
| eCl@ss 6.0 | 27144001 |
| eCl@ss 7.0 | 27144001 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000007 |
| ETIM 3.0 | EC000007 |
| ETIM 4.0 | EC000007 |
| ETIM 5.0 | EC000007 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 43172601 |
| UNSPSC 7.0901 | 31261501 |
| UNSPSC 11     | 43172601 |
| UNSPSC 12.01  | 31261501 |
| UNSPSC 13.2   | 31261501 |

### Approvals

#### Approvals

##### Approvals

UL Recognized / cUL Recognized / cULus Recognized

##### Ex Approvals

##### Approvals submitted

#### Approval details

UL Recognized 

cUL Recognized 

## Sleeve frame - VC-TR1/2M - 1852891

### Approvals

cULus Recognized  US

### Drawings

Dimensioned drawing

