

Cable housing - KGG-MC 1,5/ 7 - 1834398

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Cable housing, Pitch: 3.81 mm, Number of positions: 7, Dimension a: 29.09 mm, Color: green



Why buy this product

- For MC or IMC plugs with and without flange, and 3.81 mm pitch
- Straight cable outlet for sequencing several cable housings
- Incl. transparent label carriers from 6- to 16-pos.
- Easier plug-in and disconnection processes
- Incl. cable binders and marker strips for any numbers of positions
- Strain relief for the cables provided by cable binder or a clamp
- Full latching of both half shells of the cable housing



Key commercial data

Packing unit	10 pc
GTIN	 4 017918 051914
Weight per Piece (excluding packing)	7.79 g
Custom tariff number	85472000
Country of origin	Poland

Technical data

Dimensions

Pitch	3.81 mm
Dimension a	29.09 mm

General

Range of articles	KGG-MC 1,5
Insulating material group	I
Insulating material	ABS
Inflammability class according to UL 94	HB

Cable housing - KGG-MC 1,5/ 7 - 1834398

Technical data

General

Number of positions	7
---------------------	---

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC000879
ETIM 5.0	EC000451

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

GOST / GOST

Ex Approvals

Approvals submitted

Approval details

Cable housing - KGG-MC 1,5/ 7 - 1834398

Approvals

GOST

GOST

Accessories

Accessories

Terminal marking

Marker cards - SBS10:UNBEDRUCKT - 1007248



Marker cards, Card, white, Unlabeled, Can be labeled with: Plotter, Perforated, Mounting type: Snap into tall marker groove, Snap into flat marker groove, For terminal block width: 10 mm, Lettering field: 6 x 10.1 mm

Marking material - KGG-MC 1,5/ DST - 1839050



Transparent label carrier, can be marked with marker strips SBS 10

Drawings

Dimensioned drawing

