

PartNumber	192900-0002
Mating Cycles	200 Insertions
Product Family	Trident
Product Group	Multiway, Contact, Snap Together, Neptune, Ringlock, TNM
Component	Contact
Footnote	Dimensions are in mm (inch). Dimensions are subject to change.
For more information	Contact Cannon Sales Department
Insulation Diameter	Ø2,00 (.078) - 3,00 (.118)
Packaging	Bulk Pack (100)
Type of Contact	Pin
Contact Finish	Tin
Contact Type	Stamped
Contact Material	Copper Alloy
Contact Current Rating	16 A
Contact Resistance	5 m ohms
Contact Retention (minimum)	67 N
Wire Range mm²	0,50 - 1,50
Wire Size	20-16 AWG
Nomenclature	T2P16MC5ST
Retention Spring Material	Brass
Strip Length	3,95 ±0,25 (.155 ±.009)