

## ZNK 1/6-\*



Instrumental - Cables, 1 x 0.22mm<sup>2</sup> + spiral shield, outer diameter 6,2mm,

### Order Numbers

Black	=	ZNK 1/6-SCHWARZ
Green	=	ZNK 1/6-GRUEN
Blue	=	ZNK 1/6-BLAU
Red	=	ZNK 1/6-ROT

### Technical Information

Cable type	Unbalanced instrument cable
Outer diameter	∅ 6,2 ± 0,3 mm
Assembly	1x1x0.22 mm <sup>2</sup>
Conductor cross-section	Conductor: Cu-strand, bare 7 x 0,20
Insulation	PE, nf, Wdd. 0,30 mm
Shielding	Cu-shield, bare
Conductor impedance	≤ 90 Ω/km
Jacket colour	black, RAL 9005
Jacket material	DMC Flex PVC
Insulation impedance	≥ 104 MΩxkm
Permitted temperature range	Min.: - 5° C Max.: 50° C
Permitted bending radius	Single: 4 x diameter Multiple: 8 x diameter
Finishing	K/HS