

Datasheet

## RS Pro Portable Speaker

RS Stock No: **535-0287**



### Product Details

RS Pro portable speaker has two 165 mm speaker units designed for speech and music reproduction, providing quality sound for all requirements. It has an ABS construction for durability and is IP53 rated. The speaker frequency response ranges from 120 Hz - 20 kHz.

### Features and Benefits

- Line voltage: 50 V, 70 V and 100 V
- 20 W, 10 W, 5 W at 100 V
- 140° + 140° dispersion output
- ABS weather-resistant, IP53 rated
- Operates temperature range: -20 to +50°C
- ABS construction

**Specifications:**

Colour	White
Diameter	174 mm
Enclosure Material	ABS
Frequency Response	120 Hz to 20 kHz
Height	269 mm
Maximum Frequency Response	20 kHz
Maximum Rated Power	20 W
Minimum Frequency Response	120 Hz
Sound Pressure Level	94 dB
Weight	2.9 kg
IP Rating	IP53
Temperature Rating	-20 to +50°C