


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [85083-0300](#)
Status: **Active**
Overview: SRC - Sealed Rectangular Connectors
Description: SRC Housing, Male, Hybrid 66 Pin Mixed Power and Signal (60 x MX150™ + 6 x MX150L™), Nylon, Black

Documents:

Drawing (PDF)	Packaging Specification PK-85071-001 (PDF)
Product Specification PS-85083-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-85083-001 (PDF)	Product Literature (PDF)



General

Product Family	Crimp Housings
Series	85083
Application	Power, Signal, Wire-to-Wire
Comments	Polarized to mating part
Overview	SRC - Sealed Rectangular Connectors
Product Literature Order No	987650-7391
Product Name	SRC
UPC	883906945527

Physical

Circuits (maximum)	66
Circuits Detail	60 x MX150™ + 6 x MX150L™
Color - Resin	Black
Gender	Male
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	130.960/g
Number of Rows	12
Packaging Type	Bag
Panel Mount	Yes
Pitch - Mating Interface	0.30mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +125°C

Electrical

Current - Maximum per Contact	40A
-------------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-85083-001
Packaging Specification	PK-85071-001
Product Specification	PS-85083-001
Sales Drawing	SD-85083-300

EU RoHS ELV and RoHS Compliant REACH SVHC Contains SVHC: No Low-Halogen Status Low-Halogen	China RoHS
---	-----------------------

Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

85083Series

Mates With

85084 SRC Power Blade Housing

Use With

33000 MX™ Male Terminals. 19431 MX150L™ Male Terminal