



ENGLISH

Datasheet

## RS Pro Hanging Speaker, 10W

RS Stock No: **425-4554**



### Product Details

RS Pro hanging speaker has a maximum rated power of 10 W. The suspension wedge loudspeaker provides sound directly to where it is required. The speaker is supplied complete with hanging 'J' hooks for mounting on chains.

### Features and Benefits

- Supplied complete with hanging 'J' hooks for mounting on chains
- Chiselled profile directs sound at the requisite angle for maximum coverage
- MDF construction
- Manufactured with internal safety restraining wires with external anchoring point
- Self contained unit with screwdriver adjustment for output power settings
- 100 V line operation



ENGLISH

### Specifications:

Colour	Teak Veneer
Depth	280 mm
Frequency Response	85 Hz to 15 kHz
Height	242 mm
Maximum Frequency Response	15 kHz
Maximum Rated Power	10 W
Minimum Frequency Response	85 Hz
Sound Pressure Level	90 dB
Weight	5 kg
Width	400 mm
Line Voltage	100 V