

Datasheet

Stock No: 136-7972

RS Pro, Polychloroprene, Locating Cable Bush, 7.5mm Bundle Diameter



Image representative of range

Product Details

Protective grommets and cable grips

Manufactured from black Neoprene rubber, which withstands ozone and oil, also partly petrol and most solvents, and is poorly flammable.

Temperature range: -40 °C → +90 °C, briefly +130 °C

Dimensions (mm)			
Type	Ø Ext.	Ø Int.	Fig.
15-147	18.5	8	1
15-691	11	7	2
15-692	15	8.5	3
15-693	17.5	11	4
12-387	6	2.6	5
12-407	8.4	4	6
15-679	14	6	7
15-410	11	5.5	8
15-664	10.8	5	9
15-665	10.8	5.7	10
15-411	15	7.5	11
15-412	18.5	7.5	12

Specifications

Bushing Type	Locating Bush
Material	Polychloroprene
Maximum Bundle Diameter	7.5mm
Minimum Operating Temperature	-30°C
Maximum Operating Temperature	+90°C