


D

C

B

A



- 1 HOUSING: FLAME RETARDANT, 94V-0 RATED, GLASS FILLED NYLON OR POLYESTER, COLOR: BLACK.
CONTACTS: PHOS BRONZE.
SCREWLOCKS: ZINC.
- 2 REFER TO APPLICATION SPEC FOR RECOMMENDED P.C. BOARD MOUNTING DIMENSIONS FOR AUTOMATIC INSERTION.
- 3 CONTACTS: PLATED WITH .000030 MIN GOLD FOR LENGTH OF .055 MIN FROM MATING END, .000100 MIN TIN ON SOLDER END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
SCREWLOCKS: CLEAR CHROMATE.

COPYRIGHT 2005
TYCO ELECTRONICS CORP
ALL RIGHTS RESERVED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
G.PETERS
15SEP05

CHK
S.BOLASH
15SEP05

APD
M.WALMSLEY
15SEP05

MATERIAL
△

DIMENSIONS:
INCHES

0 PLC ± -
1 PLC ± -
2 PLC ± -
3 PLC ± .005
4 PLC ± -
ANGLES ± 2°
FINISH △

△

NAME
Tyco Electronics Corporation
Harrisburg, PA 17105-3608

PRODUCT SPEC
108-40025

APPLICATION SPEC
114-40015

SIZE
A1

CAGE CODE
00779

DRAWING NO
C=5745396

WEIGHT
-

CUSTOMER DRAWING

5745396-2
PART
NUMBER

RECEPTACLE ASSY, SIZE 2, 15 POSN,
RIGHT ANGLE, .318 SERIES, .026 DIA POSTS
W/ FEMALE SCREWLOCKS, AMPLIMITE HD-20

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
0