


## Strain relief clamp - HC-B-ZS - 1685330

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Strain relief clamps contact inserts of series: B-, BB-, D 40, D 64, DD and HV, lateral cable exit

### Key Commercial Data

|                                      |  |
|--------------------------------------|--|
| Packing unit                         | 10 pc  |
| Minimum order quantity               | 10 pc  |
| GTIN                                 | <br>4 017918 197018 |
| Weight per Piece (excluding packing) | 13.7 g   |
| Custom tariff number                 | 85389099   |
| Country of origin                    | Germany  |

### Technical data

#### Dimensions

|  |                      |
|--|----------------------|
| Clamping range of the strain relief clip | 9.00 mm ... 19.00 mm |
|--|----------------------|

#### General

|          |                   |
|----------|-------------------|
| Material | Steel, galvanized |
|----------|-------------------|

### Classifications

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 27140816 |
| eCl@ss 4.1 | 27140816 |
| eCl@ss 5.0 | 27143424 |
| eCl@ss 5.1 | 27143424 |
| eCl@ss 6.0 | 27143424 |
| eCl@ss 7.0 | 27440209 |
| eCl@ss 8.0 | 27440312 |

#### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC001121 |
| ETIM 3.0 | EC001121 |

# Strain relief clamp - HC-B-ZS - 1685330

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 4.0 | EC001121 |
| ETIM 5.0 | EC002641 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211817 |
| UNSPSC 7.0901 | 39121416 |
| UNSPSC 11     | 43172601 |
| UNSPSC 12.01  | 39121522 |
| UNSPSC 13.2   | 39121522 |

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

|     |
|-----|
| EAC |
|-----|

---