

Video surveillance kit: Digital recorder + 1 outdoor camera

Art. no. TVVR30104

Page 1 of 3

-
- Set: 4-channel recorder, 1 x day/night vision outdoor camera, universal power supply unit and 1 x 20 m coaxial cable
 - Varied camera installation options – whether indoors or outdoors
 - Simple design and high protection class (IP66)
 - Internet and mobile access to live pictures and recordings
 - 500 GB capacity for approx. 5 weeks' "non-stop" recording included
 - Simple and intuitive operation
 - Recording triggered by motion detection, schedule or permanent
 - 2 USB interfaces for quick and simple storing of important recordings.
 - Detailed high-resolution analogue recording in real time
 - Mobile access using the ABUS iDVR app
-

Video surveillance made easy

This video surveillance kit with a 4-channel recorder and built-in 500 GB hard drive, a day/night outdoor camera, universal power supply unit and coaxial cable provides video monitoring that is easy to install and operate, and can be used both indoors and outdoors.

State-of-the-art recording technology

The compact digital camera with H.264 compression and a VGA output provides 4 channels for recordings at up to 25 frames per second (real time) and 5 different resolutions (max. 960 x 576 pixels). The video images are stored in excellent quality, take up very little space on the hard drive (the recorder has a built-in 500 GB hard drive) and are optimised for fast network access. Depending on the setting, recording is started manually, according to a schedule, or by motion sensor. The kit also includes: IR camera with 600 TV lines and 3.6 mm fixed lens (angle of view: 68°) with integrated IR LEDs for day/night operation outdoors (IP66).

Fast and simple installation

Fast and easy installation is guaranteed with the 20 m combination cable and power supply unit provided.

Further information about the product:

The recorder is not compatible to the ABUS CMS software.

Video surveillance kit: Digital recorder + 1 outdoor camera

Art. no. TVVR30104

Page 2 of 3

4-Kanal Digitalrekorder

Gesamtbildrate	100 fps
Abmessungen	200 x 45 x 200 mm (B x H x T) mm
Alarmierung	Akustisches Warnsignal, OSD Signal, E-mail
Ansichten	1 / 4
Auflösung Aufnahme @ Bildrate pro Kamera	WD1, 4CIF, 2CIF, CIF, QCIF @ 25fps
Auflösung Liveansicht	VGA: 1080P: 1920*1080/60Hz, 1280*1024/60Hz, 720P: 1280*720/60Hz □ 1024*768/60Hz, BNC Output: PAL: 704×576, NTSC: 704×480
Aufnahmemodi	Manuell, Zeitplan, Bewegungserkennung
Benutzerstufen	2
Betriebsmodus	triplex
Breite	200 mm
Datensicherung	1 x USB 2.0
DDNS	Ja
Gleichzeitiger Netzwerkzugriff	128 Kameraverbindungen
Höhe	45 mm
Kompressionsstufen	6
Länge	200 mm
Leistungsaufnahme	<13W (ohne Festplatte) W
Max. Betriebstemperatur	+ 55 °C

Min. Betriebstemperatur	- 10 °C
Monitorausgänge	1x BNC (1.0 Vp-p, 75Ω), 1 x VGA
Nettogewicht	0.8 kg
Netzwerkanschluss	1 x RJ45 10/100 Mbps
Netzwerkfunktionen	Liveansicht, Wiedergabe, Datenexport
NTP	Ja
Spannungsversorgung DC	12 VDC V
Speichermedium	1 x 2,5" SATA HDD
Sprache OSD	Deutsch, Englisch, Französisch, Niederländisch, Dänisch, Italienisch, Polnisch, Spanisch, Schwedisch, Russisch
Steuerung	USB Maus
Stromaufnahme	1,5 A mA
Suchmodi	Nach Ereignis, Datum & Zeit, S.M.A.R.T
Videokanäle Analog	4
Videokomprimierung	H.264
Vor-/Nachalarmspeicher	0-30 sec. / 5-900 sec. s

500 GB 2,5" Festplatte für TVVR30004

Abmessungen	70 x 10 x 100 (B x H x T) mm
Anschlüsse	S-ATA
Breite	70 mm
Höhe	10 mm
Kapazität	500 GB

Länge	100 mm
Leistungsaufnahme	max. 1,4 W
Max. Betriebstemperatur	60 °C
Min. Betriebstemperatur	0 °C
Nettogewicht	0.12 kg

Video surveillance kit: Digital recorder + 1 outdoor camera

Art. no. TVVR30104

Page 3 of 3

Tag/Nacht Mini Außenkamera

Abmessungen	150 x 70 mm
Anschlüsse	Videosignal (BNC), Spannungsversorgung (DC)
Bildaufnehmer	1/3" DIS
Bildelemente (effektiv)	720 (H) x 480 (V) Pixel
Blende bei Mindestbeleuchtung (Farbe)	0,1 Lux
Blende bei Mindestbeleuchtung (IR)	0 Lux
Electronic-Shutter	1/25 ~ 1/15.000 sek.
Gegenlichtkompensation	Ja
Höhe	150 mm
Horizontaler Blickwinkel	68,4 °
IR-LEDs	12
IR-Reichweite	10 m
Kameratyp	Tag/Nacht - Außenkamera
Max. Betriebstemperatur	+ 50 °C

Max. Luftfeuchtigkeit	max. 90 %
Min. Betriebstemperatur	- 20 °C
Nettogewicht	0.36 kg
Objektiv	3.6 mm, Fix-Objektiv mm
Rauschunterdrückung	> 52 dB
Schutzart IP	66
Spannungsversorgung DC	12 V
Stromaufnahme	max. 420 mA
Tag-/Nachtumschaltung	Elektromechanischer IR-Cut Filter
TVL	600 TVL
Videosystem	PAL / NTSC