

## Datasheet

# RS Pro On/Off Temperature Controller, 96 x 96mm, PT100 Input, 24 V ac Supply

RS Stock No: 875-1289



## Product Details

RS Pro on/off temperature controller measuring 96 x 96 mm works with PT100 input using 24 V ac supply. Controller gives voiced warning via internal buzzer and comes with 2 & 3 digit display for time value and temperature value.

## Features and Benefits

- 2 & 3 digit display for time value and temperature value
- On/Off or proportional control form selection
- Working time selection in minutes or seconds
- Hysteresis adjustment
- Voiced warning via internal buzzer
- Cover switch input
- Steam output (875-1270 & 875-1289 only)
- 24V & 230V supply voltages supported
- IP65 protection (front panel only)

**Specifications:**

Input Type	PT100
IP Rating	NEMA 4X
Maximum Operating Temperature	+50°C
Minimum Operating Temperature	0°C
Mounting Type	1/4 DIN Rail
Number of Inputs	1
Number of Outputs	2
Output Type	SSR
Panel Depth	96 mm
Size	96 x 96 mm
Supply Voltage	24 V ac
Termination Type	Screw
Panel Cut Out Size	92 x 92 mm