





NOTE:
 1 MATERIAL:
 1-1 HOUSING : LCP, 30% G/F, UL 94V-0, BLACK
 1-2 SIGNAL TERMINAL AND DETECT TERMINAL : PHOSPHOR BRONZE
 1-3 METAL SHELL : STAINLESS STEEL
 2 FINISH:
 2-1 SIGNAL TERMINAL : 1.25-6.25 MICRON NICKEL MIN UNDER-PLATED,
 0.75-1.25 MICRON GOLD MIN ON CONTACT AREA, GOLD FLASH PLATED ON SOLDER AREA
 2-2 METAL SHELL : GOLD FLASH PLATED OVER NICKEL ON SOLDER AREA
 2-3 DETECT PIN : 1.25-6.25 MICRON NICKEL MIN UNDER-PLATED
 GOLD FLASH PLATED ON CONTACT AREA, TIN PLATED ON SOLDER AREA
 3 PRODUCT SPECIFICATION: PS-47309-001.



473093751	3.75	2.55
473093551	3.55	2.35
473093351	3.35	2.15
473092851	2.85	1.65
473092651	2.65	1.45
PART NUMBER	DIMENSION A	DIMENSION B

REVISION	EC NO. : SH200806090399	2008/02/22	DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION		
	DRWN: LLIU10	2008/03/11				MM ONLY		15:1	METRIC	◎ □		
	CHKD: YLZH02	2008/04/02				mm	INCH	DRAWN BY		DATE	TITLE	
	APPR: HWANG					4 PLACES ± --- ± ---		XIXU		2005/12/24	TFR HEADER W/DETECT PIN	
						3 PLACES ± --- ± ---		CHECKED BY		DATE		
						2 PLACES ± 0.15 ± ---		Y JWU		2005/12/24	MOLEX INCORPORATED	
						1 PLACE ± 0.25 ± ---		APPROVED BY		DATE		
						ANGULAR ± 1 °		Y JWU		2005/12/24		
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.	SHEET NO.	
								SEE TABLE		SD-47309-001	1 OF 2	
				SIZE A2		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

