




Alphabetical Picture Part Number
SEARCH **SEARCH** **SEARCH**

Go To Step Search™ Screen

35664 -- 1 of 1 products

Terminals and Splices
Ring and Spade Tongue Terminals

General **INFO**
Sales **INFO**
Customer Drawings **SPECIFICATIONS**



Line art represents typical product only.

<i>Searchable Features:</i>	
Terminal Shape	Ring Tongue
Body Style	SOLISTRAND
Receptacle Style	Straight
Barrel Type	Closed Barrel
Wire/Cable Type	Regular Wire
Wire Range	8 [6.64 - 10.5 ²] AWG [mm]
Wire Range (CMA)	13,100-20,800
Insulation	No
Insulation Support	Non-Insulation Support
Stud Size	1/2 [M12]
Stud Diameter	.500 [12.70] in. [mm]
Shape	RING-048
Heavy Duty	Standard
Packaging Method	Loose Piece
Material	Copper
Finish	Tin
<i>Other Properties:</i>	
Dim. C	1.000 [25.40] Min. in. [mm]
Dim. E	1.337 [33.96] Max. in. [mm]
Dim. L	1.965 [49.91] Max. in. [mm]
Dim. W	1.250 [31.75] in. [mm]
Barrel I.D. Min.	.172 [4.37] in. [mm]
Stock Thickness	.051 [1.30] Max. in. [mm]
CERTI-CRIMP Hand Tool	69355-0, 59975-1
Pneumatic Hand Tool Number	69010, 69015-0, 69012-0
Crimping Head for Pneumatic Tool # 69010-0	38394-0
Crimping Head for Pneumatic Tool # 69012-0	674327-0
Crimping Head for Pneumatic Tool # 69015-0	49956-0
DYNA-CRIMP Tool Number	69120-2
Crimping Head for DYNA-CRIMP Tool # 69120-2	69065-0
Upper Die for DYNA-CRIMP Crimping Head # 69065-0	48126-0
Lower Die for DYNA-CRIMP Crimping Head # 69065-0	48355-0