

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [19199-0009](#)  
**Status:** **Active**  
**Overview:** [Splices](#)  
**Description:** Butt - Window Splice for 14-16 AWG Wire

**Documents:**

[Drawing \(PDF\)](#) [Product Specification PS-19902-013 \(PDF\)](#)  
[Product Specification PS-19902-011 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Splices
Series	<a href="#">19199</a>
Comments	Mil Spec M7928/5-4
Crimp Quality Equipment	Yes
Mil-Spec	M7928/5-4
Overview	<a href="#">Splices</a>
Product Name	Butt - Window
UPC	800753046825

**Physical**

Barrel Type	Closed
Color - Resin	Blue
Insulation	Nylon (PA)
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.528/g
Packaging Type	Bag
Temperature Range - Operating	-55°C to +105°C
Wire Insulation Diameter	4.32mm max.
Wire Size AWG	14, 16
Wire Size mm <sup>2</sup>	1.30 - 2.00

**Electrical**


Voltage - Maximum	300V
-------------------	------

**Material Info**

Old Part Number	WB-841
-----------------	--------

**Reference - Drawing Numbers**

Product Specification	PS-19902-011, PS-19902-013
Sales Drawing	SD-19199-003



**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

Not Reviewed

**Low-Halogen Status**

Not Reviewed

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[19199Series](#)