



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		T7	REVISED PER ECO-12-002693	13FEB12	KH	DR



STYLE A



STYLE B
INSULATION RESTRICTING

- 1
- STAMP "AMP - SEE TABLE" APPROX AS SHOWN

2

3

4

5

6

7

8

9

10

11

12

13

OBSOLETE	50	LOOSE PIECE, BOX	10	.115-.200	10	BROWN	B	4	6	9-320568-2
	50	LOOSE PIECE, BOX	12	.095-.200	12	YELLOW	B		6	8-320568-2
	50	LOOSE PIECE, BOX	12-10	.150-.230	12-10	--	A		5	7-320568-2
	500	ON TAPE, LG. BOX	12-10	.150-.230	12-10	--	A		5	2-320568-6
	---	LOOSE PIECE	10	.119-.200	10	BROWN	B	4	6	2-320568-3
	---	LOOSE PIECE	12	.095-.200	12	YELLOW	B		6	2-320568-2
	2500	ON TAPE & REEL	12-10	.150-.230	12-10	--	A		5	2-320568-1
	---	LOOSE PIECE	12-10	.150-.230	12-10	--	A		5	320568
QTY	PACKAGE TYPE		STAMPING	WIRE INSUL DIA	WIRE SIZE	STRIPE COLOR	STYLE	BODY FINISH	SLEEVE	PART NO

CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 105°C MAX		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 17DEC09		 TE Connectivity				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: 300 VOLT MAX		DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± ±	CHK T MICHELUTTI 17DEC09	APVD T MICHELUTTI 17DEC09	NAME				
			TERMINAL, RING TONGUE, PIDG WIRE SIZE: 12-10 AWC										
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 2.62-6.64mm² [5,180-13,100] STRANDED OR SOLID	MATERIAL	FINISH	WEIGHT	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
FOR ORDER ENTRY	1-800-526-5142		THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	-	-	-	A2		00779	C=320568		-	
CUSTOMER DRAWING							SCALE	5:1	SHEET	1 of 1	REV	T7	