

Housing - HC-B 10-TFQ-N-O1PG16S - 1460068

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



HEAVYCON B10 sleeve housing, for double locking latch, height: 56 mm, with 1 x Pg16 gland, lateral cable outlet



Key commercial data

Packing unit	10 pc
GTIN	 4 046356 695640
Weight per Piece (excluding packing)	22.22 g
Custom tariff number	85389099
Country of origin	Germany

Technical data

Dimensions

Height	56 mm
Width	43 mm
Length	73 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-B10, BB18, DD42, M, K8/24
Type	B10
Housing type	Sleeve housing
Locking type	For double locking latch
No. of cable outlets	1
Cable exit	Lateral
Screw connection	none
Type of the screw connection	1x Pg16
Housing material	Aluminum die-cast

Housing - HC-B 10-TFQ-N-O1PG16S - 1460068

Technical data

General

Housing surface material	Powder-coated, gray
--------------------------	---------------------

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approvals submitted

Approval details

EAC

Housing - HC-B 10-TFQ-N-O1PG16S - 1460068

Accessories

Accessories

Full screw connection

Cable gland - G-INS-PG16-S68N-PNES-GY - 1411144



Cable gland, Cable gland material: Polyamide, External cable diameter 10 mm ... 14 mm, Shielding: No, Connecting thread: Pg16, Color: silver grey

Cable gland - G-INS-PG16-S68N-NNES-S - 1411174



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 10 mm ... 14 mm, Shielding: No, Connecting thread: Pg16, Color: silver

Cable gland - G-INSEC-PG16-S68N-NNES-S - 1411199



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 10 mm ... 14 mm, Shielding: Yes, Connecting thread: Pg16, Color: silver

Plug for cable screw gland

Filler plugs - HC-BS-PG16 - 1674516




Filler plugs, for Pg screw connections, type Pg16

Drawings

Housing - HC-B 10-TFQ-N-O1PG16S - 1460068

Dimensioned drawing



Dimensional drawing

Phoenix Contact 2015 © - all rights reserved
<http://www.phoenixcontact.com>