

# Specifications for BMP71 Label Printer Labels

<b>Adhesive</b>	Permanent Acrylic
<b>Application</b>	Voice & Data Communication
<b>Approval/Compliance</b>	UL Recognised;CSA Accepted;Halogen Free (DIN VDE 0472/part 815)
<b>Article No.</b>	114705
<b>Brady Material No.</b>	<a href="#">B-425</a>
<b>Material Type</b>	Polypropylene
<b>Brand</b>	WorkHorse™ Series
<b>Colour</b>	White
<b>Finish</b>	Matt
<b>Description</b>	Flags for the BMP™71 Label Printer.
<b>Max. Characters per Line</b>	29
<b>Max. Lines of Text</b>	4
<b>Max. Service Temp. °C</b>	80
<b>Order Reference</b>	M71FP-1-425
<b>Printer Compatibility</b>	BMP71
<b>Ribbon Series</b>	M71-R4300
<b>Shape</b>	Rectangle
<b>Size - Height (mm)</b>	10.00
<b>Size - Width (mm)</b>	30.00
<b>Additional Information</b>	Excellent solvent resistance
<b>Total Qty per Pack</b>	250 Label(s) / Box
<b>Vertical Repeat (mm)</b>	23.50
<b>Voice/Data Application</b>	Fibre Optic Labels/Flags
<b>Industry</b>	Data & Telecommunications;Electrical

<b>Min. Service Temp. °C</b>	-70
<b>QTY. per Row</b>	1
<b>Thickness (mm)</b>	0.1143