

Cable - CABLE-D-15SUB/M/OE/0,25/S/4,0M - 2926483

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Shielded cable with a 15-pos. D-SUB pin strip and one open end. The individual wires are labeled 1 to 15 and fitted with ferrules. The braided shield is routed to a separate cable end. Cable length: 4 m.




The figure shows the 25-pos. version

Why buy this product

- Individual wire marking: 1, 2, 3, 4, etc.
- Individual wires fitted with ferrules
- Connector according to IEC 60807-2/DIN 41652
- Shield connection: H05V-K 1 mm² cable, black, 0.5 m in length
- D-SUB socket or pin strip at one end
- Open end at one end
- 1:1 connection
- Screw connection: 2 UNC 4-40 screws

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 548199
Weight per Piece (excluding packing)	333.33 g
Custom tariff number	85444290
Country of origin	Germany

Technical data

General

Nominal voltage U _N	125 V AC/DC
Max. current carrying capacity per path	2 A
Max. conductor resistance	≤ 0.09 Ω/m
Length of cable	4 m
Single wire, cross section	0.25 mm ²
AWG	24
External diameter	9 mm
Shielding	yes
	Tinned copper-braided shield, approx. 85% covering

Cable - CABLE-D-15SUB/M/OE/0,25/S/4,0M - 2926483

Technical data

General

Insertion/withdrawal cycles	> 200
-----------------------------	-------

Environmental conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Flame resistance	IEC 60332-1

Connector, module side

Number of positions	15
Connectors	D-SUB pin strip
Number of plugs	1

Connector, controller side

Number of positions	15
Connectors	Open end
Number of plugs	0

Classifications

eCl@ss

eCl@ss 4.0	27060306
eCl@ss 4.1	27060306
eCl@ss 5.0	27061801
eCl@ss 5.1	27061801
eCl@ss 6.0	27061801
eCl@ss 7.0	27061801
eCl@ss 8.0	27061801

ETIM

ETIM 2.0	EC000237
ETIM 3.0	EC000237
ETIM 4.0	EC000237
ETIM 5.0	EC000237

UNSPSC

UNSPSC 6.01	26121620
UNSPSC 7.0901	26121620
UNSPSC 11	26121620
UNSPSC 12.01	26121620
UNSPSC 13.2	26121620

Approvals

Approvals

Cable - CABLE-D-15SUB/M/OE/0,25/S/4,0M - 2926483

Approvals


Approvals


UL Recognized / cUL Recognized / cULus Recognized

Ex Approvals

Approvals submitted

Approval details

UL Recognized 

cUL Recognized 

cULus Recognized 